

### 8590 PEDESTAL

#### TO BE USED FOR 8536 CONTROLLERS ONLY.


# The 8590 pedestal measurements are as follows:

23.25" high by 15.20" wide by 3.98" deep

**NOTE:** The controller should be placed in an environment not subject to direct sprinkler spray or continuous heavy moisture.

#### PEDESTAL MOUNTING

Mount the pedestal utilizing the four mounting holes at its base. The holes are 11/32" diameter for the use of 5/16" bolts or lag screws. The holes are positioned as show below.



#### CONTROLLER MOUNTING TO PEDESTAL

- 1. Remove door of pedestal by unlocking and tilting it away from the pedestal while lifting it up.
- 2. Open door of controller and remove painted panel from inside the 8536, for access to conduit holes.
- 3. Install finishing plug to existing 7/8" diameter conduit hole.
- 4. Place controller on top of pedestal aligning two holes to top of pedestal.

  Using center hole, install the 1-1/4" close nipple with locknuts to hold controller to pedestal. Keep controller flush to back flange while tightening locknuts.

## **INSTALLATION KIT**

### Modifications to 8536 case - Relocation of AC hole

- 1. Following template below, add second 1/2" conduit hole (Ø7/8") to dimension shown.
- 2. Plug existing hole with snap-in plug. (provided)

